

signotec Sigma LITE

Highlights & Data Sheet











HIGHLIGHTS

- Cost-efficient signature pad without display 10,4 cm (4") active signing area.
- Special signing surface for precise signature capturing.
- Signature capturing with 500 Hz 4D samples and 1.024 pressure stages (x, y, z, t).
- Including free of charge software packages.
- Unique RSA-signature creation and RSA-encryption methods inside the pad.
- Secure Mode to display the signature on the screen in realtime.
- Various options for the secure management of certificates and keys in the pad.
- Delivery comes with completely assembled USB cable, pen and cord.









Page 3 of 5

TECHNICAL DATA

© 2000 - 2024 signotec GmbH

General data	
Dimensions	160 x 120 x 10 mm (W x D x H)
Casing colours	Upper shell: RAL 9005, jet black Lower shell: RAL 9005, jet black
Cable port	USB
Cable length	Approx. 2 meters
Power consumption	Standby-status: <500 μ A Running: 20mA
Power supply	USB
Status-LED	2 coloured and freely programmable LEDs
Stand	Mounting stand on the backside, compatible Multigrip™ plate available.
Weight	Approx. 170 grams (incl. cable)
Warranty	2 years, optional extension up to 5 years.
Country of origin	Germany

Display	
Туре	Plastic surface for signature capturing.
Size	4" (10,4 cm)
Colour space	No
Backlight	No
Configuration of backlight	No
Resolution	No
Pixel size	No
Visible area	No
Line of sight	No
Scroll-function	No

Sensor			
Туре	Resistive Touch Panel (RTP)		
Active signing area	91 x 45 mm		
Resolution	4.096 x 4.096 pixels ≙ 2.214 x 1.130 ppi		
Linearity	± 1,5% in x-, y- and z- direction		
Method of input	Special sensor for pen input		
Surface	Special signing surface with wear-protection.		
Surface hardness	No		
Life expectancy	Approx. 2 million signatures		
Pressure stages	1.024 pressure stages		
Output rate of coordinates	500 Hz 4D-samples (x, y, z, t)		
Internal sampling rate	6.000 samples per second		
Stability of output rate	Constant through integrated quartz		
Pen	Battery-less pen with special, spring-loaded lead (changeable).		
Life expectancy of the pen	Approx. 150.000 signatures at 250 grams pressure and 2,5 cm length.		
Pen tilt angle	No		
Possible height of the pen	No		
Pen attachment	Highly flexible textile-cord and horizontal pen holder. (assembled at the factory)		

Data Sheet signotec Sigma LITE



Connection types	
USB	HID-USB and WinUSB
Serial	Optional with internal USB-Serial-Converter (VCOM-Port) using FTDI or chargeable VCOM-Port-Driver.
USB-Standby-Support	Yes, if the corresponding signal is given, the device switches off.
Ethernet	Yes, with an optionally available USB-to-Ethernet adapter.

Driver and Software	
Driver	No special driver is required for a USB connection.
Plug and Play	Yes, available for all connection types.
SDK (API)	Several SDKs including updates and support available.
Tools	Tools free of charge including updates and support.
Software	Further chargeable software available.

System environment	
Operating System	Windows 10 or newer, Windows Server 2016 or newer (RDP, Citrix), Linux
Terminal Server and Citrix	Compatible with Windows Remote Desktop and Citrix ICA
Citrix Virtual Channel	Optionally available

Security mechanisms	
Data transfer	AES-256 encrypted data transfer between host and pad via RSA key exchange.
Encryption	RSA-Encryption unit inside the pad.
Firmware	Flash memory is protected against data theft.
Secure Mode	Real-time display of the signature without usable biometrics.
Signature unit	RSA signature creation unit in the pad.
Key storage	Creation and storage of certificates in the pad.
Key size	4096 Bit
Certificate Signing Request (CSR)	CSR can be generated in the pad and extracted.
Trusted certificates	The CSR can be signed by a root authority. Additional information: eIDAS Organisation Seal
Supported Hash-algorithms	SHA-1, SHA-256 und SHA-512
Signature-Performance	Transmission and Signing of a SHA-256 Hash via WinUSB: 2048 Bit: 850 ms; 3072 Bit: 2.500 ms; 4096 Bit: 5.600 ms
signotec "Content-Signing"	No
Protection against forceful break in	The casing can be glued optionally.
signotec "Content-Signing"	2048 Bit: 850 ms; 3072 Bit: 2.500 ms; 4096 Bit: 5.600 ms No

Miscellaneous	
Individualization	Change of casing colour and logo print (on request).
Slideshow	Not applicable
Certifications and standards	CE, FCC, DIN EN 60950-1, DIN EN 61000-6-1, EN 61000-6-3, EN 55022, EN 55024
RoHS	RoHS-compliant according to EU-regulations.
WEEE-RegNo. (German register for used devices)	DE 41995888
Packaging law RegNo.:	DE 3470684644700
Serial number	Unique and retrievable, internal serial number.
Device label	There is a label on the packaging and the device with information regarding the article number, hardware revision and serial number, including a barcode.



Operating and storage conditions	
Operating temperature	-10°C to +60°C
Storage temperature	-25°C to +70°C
Air humidity for operation and storage	<= 90%, non-condensing
Air pressure for operation and storage	> 700 hPa
Degree of protection	IP 52

Reliability / Quality assurance		
Quality test	Individual testing of devices with test log.	
High temperature test of the components	240 hours at 80°C	
Low temperature test of the components	240 hours at - 40°C	
Humidity test of the components	240 hours at 60°C and 90% humidity	
Thermal shock test of the components	30 minutes at – 40°C and directly 30 minutes at + 80°C (10x in succession)	

Article numbers	
ST-LTE105-2-U100	signotec Sigma Lite with HID-USB and approx. 2 m USB-cable
ST-LTE105-2-FT100	signotec Sigma Lite with FTDI (VCOM) and approx. 2 m USB-cable

Copyright

Copyright © 2000 - 2024 signotec GmbH

All rights reserved. This documentation and the components described therein are copyrighted products of signotec GmbH Ratingen in Germany. Partial or full reproduction is only permitted with the written consent of signotec GmbH. All hardware and software names used are trade names and / or trademarks of the respective manufacturers / owners. Subject to changes at any time. We accept no liability for errors in the documentation.

© 2000 - 2024 signotec GmbH	Data Sheet signotec Sigma LITE	Dogo 5 of 5
© 2000 - 2024 Sidilotec Gillon	Data Sheet Signoted Signa Life	Page 5 of 5